
BACK-ROLLER PLUS

Rearpannier with roll dosure and QL2.1-system



Additional fastening with strap, buckle and D-ring

Auxiliary dosure with webbing and buckle, upper fixation point for the shoulder strap flap

Hook with webbing for both closure options

Rolling closure

Buckles for closing the rolling closure at the top or for attaching the shoulder strap

Waterproofouter pocket with roll / flap dosure

Twolateral 3M Scotchlite reflectors













Release handle for mounting and releasing the QL2.1 system Injection-molded auxiliary fastener for fixing the handle


Exchangeablehook inserts in sizes 8, 10 and 12 mm

PEinner stiffening panel is prepared for Pannier stabilizing insert

> Slidable and rotatable hook (15° steps) with anti-scratch function

> > Hook rail made of two-component synthetic with anti-scratch function

Edgeprotector with slots for mounting the Pannier Carrying System



| Height cm/in | Width cm/ in | Depth cm/ in | Volume L/cu.in. | Weight g/oz. | max. capacity kg/lbs. |
|--------------|--------------|--------------|---------------------|--------------|-----------------------|
| 42/16.5 | 23/32 9/12.6 | 17/6.7 | 20 + 3 / 1220 + 183 | 910 / 30.7 | 9/19.8 |

SPECIFICATIONS:

- + Classical rear pannier with roll closure
- + Abrasion restistant Cordurafabric
- + QL2.1 system for racks up to 16 mm
- + Upper QLhook and lower sliding hook adjustable without tools
- + Including reduction pieces for tube diameters 8, 10 and 12 mm; with anti-scratch function reducing abrasions on rack
- + Outer pocket with additional 3L volume
- + Lowerhook rail made of two-component "hard-soft" synthetic reduces abrasions on carrier
- + Including integrated inner pocket
- + Shoulder strap with flap that allows direct fixation of the strap to the bag
- + Can be used right or left due to symmetrical shape
- + Can be combined on the rack with ORTLIEBRack-Packsize 24 Lor 31 L
- + Highly reflective Scotchlite reflector
- + Easyto clean inside

Contents: Pannierwith shoulder straps and reduction inserts for 8, 10 and 12 mm

Optional accessories: Pannier Stabilizing Insert, Packing Cubes/Pannier Commuting Insert, Pannier Carrying System, Anti-Theft-Device (E125), Outer Pocket 2,1 L, Mesh-Pocket, Bottle-Cage, QL2.1 hook 18mm (E211) & 20mm (E193)

Attention: Maximumload per pannier is 9kg / 20 lbs. Werecommendweighing each loaded pannier to confirm that the maximum allowance of the pannier fixation is not exceeded. This practice is advised for both rear and front panniers. CAUTION:Themaximumweightcapacity of every carrier model is different. Please observe the maximumweight allowance of the carrier fitted to your bicycle. Note: Sometimes the maximum capacity of the panniers fixing system can exceed the maximum capacity of the carrier. DONOTexceed the maximum capacity of the carrier! Note, that the use of panniers will significantly influence the handling properties of your bicycle.

Attention: As abrasion cannot be ruled out, we recommendthat all points wherethe mounting system contacts the bicycle rack or frame be protected by scratch protection film.

INDICE In order to meet standard IP64 (6=dustproof 4=protected against splash water coming from all directions) the lid must be rolled 3.4 times.


ORTLIEBSport art ikel GmbH · Rainstrasse 6 · 91560 · Heilsbronn, Germany · T + 49 9872 800-0 · F + 49 9872 800-266 · E info@ortlieb.com · www.ortlieb.com





BACK-ROLLER PLUS


- MONTAGEANLEITUNG
- **GB** ASSEMBLY INSTRUCTIONS
- FR INSTRUCTIONS DE MONTAGE
- ISTRUZIONI DI MONTAGGIO NL
 - MONTAGE HANDLEIDING
- DK MONTERINGSVEJLEDNING
- ES INSTRUCCIONES DE MONTAJE SE MONTERINGS ANVISNING
- NO MONTERINGS ANVISNING
- FI ASENNUSOHJEET PL INSTRUKCJA MONTAZU
 - JP 装着方法






















WK 170 3623

